

Lewatit® MonoPlus MP 500 is a strongly basic, macroporous anion exchange resin (type I) with beads of uniform size (monodisperse) based on a styrene-divinylbenzene copolymer, designed for all demineralization applications.

The monodisperse beads have high chemical and osmotic stability. The extremely high monodispersity and very low fines content result in particularly low pressure losses compared with standard resins. Due to its special macroporous structure, **Lewatit® MonoPlus MP 500** stands for effective adsorption and desorption of naturally occurring organic substances.

Lewatit® MonoPlus MP 500 is especially applicable for:

- » the demineralization of water for industrial steam generation, e.g. Lewatit® WS System, Lewatit® Liftbed System or Lewatit® Rinsebed System
- » polishing using the Lewatit® Multistep System or a conventional mixed bed arrangement in combination with **Lewatit® MonoPlus SP 112** or **Lewatit® MonoPlus SP 112 H**
- » condensate polishing in combination with **Lewatit® MonoPlus SP 112 H**

Lewatit® MonoPlus MP 500 adds special features to the resin bed:

- » high flow rates during regeneration and loading
- » a good utilization of the total capacity
- » a low rinse water requirement
- » a homogenous throughput of regenerants, water and solutions, resulting in an homogenous operating zone
- » a virtually linear pressure drop gradient across the entire bed depth, allowing operation with higher bed depths
- » a good separation of the components in mixed bed applications

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess Corporation.

PRODUCT INFORMATION

LEWATIT® MonoPlus MP 500



Common Description

Delivery form	Cl ⁻
Functional group	quaternary ammonium type 1
Matrix	styrenic
Structure	macroporous
Appearance	beige, opaque

Specified Data

		US Units			
Uniformity coefficient				max.	1.1
Mean bead size	d50			mm	0.62 (+/-0.05)
Total capacity (delivery form)		kg/ft ³	24.0	min. eq/L	1.1

This document contains important information and must be read in its entirety.

Edition: 2023-01-19
Previous Edition: 2020-10-23

PRODUCT INFORMATION

LEWATIT® MonoPlus MP 500



Typical Physical and Chemical Properties

		US Units		Metric Units	
Bulk density for shipment	(+/- 5%)	lb/ft³	40.0	g/L	640
Density				approx. g/mL	1.06
Water retention (delivery form)				approx. weight %	60-65
Volume change (Cl⁻ -OH⁻)				max. approx. %	+22
Stability pH range					0-14
Storage time (after delivery)				max. years	2
Storability temperature range				°C	-20 - +40

Operation

		US Units		Metric Units	
Operating temperature		max. °F	158	max. °C	70
Operating pH range	during exhaustion				0-12
Bed depth for single column		min. inches	31.5	min. mm	800
Bed depth per component in mixed bed		min. inches		min. mm	500
Back wash bed expansion per m/h (20°C)				%	13
Specific pressure loss (15°C)				kPa*h/m²	0.8
Max. pressure loss during operation		PSI	44	kPa	300
Specific flow rate		max. gpm/ft³	13	max. BV/h	100

Regeneration

		US Units		Metric Units	
NaOH regeneration	concentration	approx. wt. %		approx. wt. %	2-6
NaOH regeneration	quantity co-current	min. lb/ft³	5.0	min. g/L resin	80
NaOH regeneration	quantity counter-current	min. lb/ft³		min. g/L resin	50
Regeneration contact time		min. minutes		min. minutes	20
Slow rinse at regeneration flow rate		min. gal/ft³	15.0	min. BV	2
Fast rinse at service flow rate		min. gal/ft³	15.0	min. BV	2

This document contains important information and must be read in its entirety.

Edition: 2023-01-19
Previous Edition: 2020-10-23

Additional Information & Regulations

PRODUCT SAFETY INFORMATION REQUIRED FOR SAFE USE OF PRODUCTS MENTIONED HEREIN IS NOT INCLUDED IN THIS DOCUMENT. BEFORE HANDLING ANY PRODUCT, ALWAYS READ PRODUCT AND SAFETY DATA SHEETS AND CONTAINER LABELS FOR SAFE USE, PHYSICAL AND HEALTH HAZARD INFORMATION.

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Packaging

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described within the product safety information. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.

PRODUCT INFORMATION

LEWATIT® MonoPlus MP 500



The manner in which you use and the purpose to which you put and utilize our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations are beyond our control. Therefore, it is imperative that you test our products, technical assistance and information to determine to your own satisfaction whether they are suitable for your intended uses and application. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us. Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale. All information and technical assistance is given without warranty or guarantee and is subject to change with notice. It is expressly understood and agreed that you assume and hereby expressly release us from liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information. Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent.

Health and Safety Information: Appropriate literature has been assembled which provides information concerning the health and safety precautions that must be observed when handling the LANXESS Corporation products mentioned in this publication. For materials mentioned which are not LANXESS Corporation products, appropriate industrial hygiene and other safety precautions recommended by their manufacturers should be followed. Before working with any of these products, you must read and become familiar with the available information on their hazards, proper use, and handling. This cannot be overemphasized. Information is available in several forms, e.g., *safety data sheets and product labels*. Consult your LANXESS Corporation representative or contact the Product Safety and Regulatory Affairs Department at LANXESS Corporation

Regulatory Compliance Information: Some of the end uses of the products described in this publication must comply with applicable regulations, such as the FDA, BfR, NSF, USDA, and CPSC. If you have any questions on the regulatory status of these products, contact - for business in the USA - the LANXESS Corporation Regulatory Affairs and Product Safety Department in Pittsburgh, PA, USA or for business outside US the Regulatory Affairs and Product Safety Department of LANXESS Deutschland GmbH in Germany.

Note: The information contained in this publication is current as of the date of edition. Please contact LANXESS Corporation Inc. to determine if this publication has been revised.

LANXESS Corporation
111 RIDC Park West Dr
12275-1112 Pittsburgh-Allegheny
USA

+1-800-678-0020
lewatit@lanxess.com

www.lanxess.com
www.lpt.lanxess.com

This document contains important information and must be read in its entirety.

Edition: 2023-01-19
Previous Edition: 2020-10-23